



MATERIALS OF CONSTRUCTION

END FITTINGS - CARBON STEEL - SCH 40/STD WT
 HOSE & BRAID - STAINLESS STEEL - 300 SERIES
 ELBOWS - CARBON STEEL - SCH 40/STD WT

NOTE: V-LOOPS 2" AND LARGER INSTALLED IN ANY ORIENTATION OTHER THAN HANGING DOWN MUST HAVE THE 180° RETURN SUPPORTED. (SEE INSTALLATION INSTRUCTIONS.)

CONTACT FACTORY FOR ADDITIONAL SIZES AND MOVEMENTS. ALL DIMENSIONS IN INCHES.

QTY	SIZE	MODEL	MOVEMENT	A	B	PSI @ 70° F	WT (LBS)	PROJECT INFO
	2" (50mm)	VLF80200	+/- 4"	31.75"	14.25"	516	16	
	2.5" (65mm)	VLF80250	+/- 4"	38"	16.875"	387	24	
	3" (80mm)	VLF80300	+/- 4"	41"	18.125"	316	30	
	4" (100mm)	VLF80400	+/- 4"	47.375"	20.75"	232	46	
	5" (125mm)	VLF80500	+/- 4"	53.5"	23.125"	191	68	
	6" (150mm)	VLF80600	+/- 4"	60"	25.625"	165	95	
	8" (200mm)	VLF80800	+/- 4"	70.125"	29.125"	234	186	
	10" (250mm)	VLF81000	+/- 4"	82.5"	33.875"	230	287	
	12" (300mm)	VLF81200	+/- 4"	94.5"	38.375"	161	412	

NSF 372 - LEAD FREE

The wetted surface of this product contacted by consumable water contains less than one quarter of one percent (0.25%) of lead by weight. Material complies with state codes and standards, where applicable, requiring reduced lead content.

CUSTOMER: _____

PROJECT: _____

ENGINEER: _____

REV.	DATE
2323 W. HUBBARD ST. CHICAGO, IL 60612 TEL: 312-738-3800 WWW.METRAFLEX.COM	
METRAFLEX V-LOOP FLANGED ENDS, +/- 4" MOVEMENT	
DRAWN BY: SMARTEN	DATE: 7/29/2015
APPROVED: DKISH	DATE: 8/3/2015
SCALE: NONE	DRAWING NUMBER: VLF8