



MATERIALS OF CONSTRUCTION

END FITTINGS - CARBON STEEL - SCH 40/STD WT
 HOSE & BRAID - STAINLESS STEEL - 300 SERIES
 90° ELBOW - CARBON STEEL - SCH 40/STD WT
 180° RETURN - CARBON STEEL - SCH 40/STD WT

NOTE: METRALOOPS 2" AND LARGER INSTALLED IN ANY ORIENTATION OTHER THAN HANGING DOWN MUST HAVE THE 180° RETURN SUPPORTED. (SEE INSTALLATION INSTRUCTIONS.)

CONTACT FACTORY FOR ADDITIONAL SIZES AND MOVEMENTS. ALL DIMENSIONS IN INCHES.

QTY	SIZE	MODEL	MOVEMENT	A	B	PSI	WT (LBS)	PROJECT INFO
	0.5" (12.5mm)	MLUT80050	+/- 4"	13"	15"	300	5.5	
	0.75" (20mm)	MLUT80075	+/- 4"	13.25"	18"	300	5.5	
	1" (25mm)	MLUT80100	+/- 4"	15"	20"	300	8	
	1.25" (32mm)	MLUT80125	+/- 4"	15.75"	21"	300	10	
	1.5" (40mm)	MLUT80150	+/- 4"	17.5"	23"	300	14.5	
	2" (50mm)	MLUT80200	+/- 4"	20"	25"	300	18	
	2.5" (65mm)	MLUT80250	+/- 4"	21.5"	28"	300	29	
	3" (80mm)	MLUT80300	+/- 4"	24"	30"	300	43	
	4" (100mm)	MLUT80400	+/- 4"	30"	35"	175	55	

SUITABLE FOR USE IN DRY PIPE SYSTEMS FOR TEMPERATURES TO -40°F.

CUSTOMER: _____

PROJECT: _____

ENGINEER: _____

2	SUPPORT BRACKET NOTE	1/21/2016
REV. 1	SUPPORT BRACKET CHANGE	DATE 2/5/2015
		2323 W. HUBBARD ST. CHICAGO, IL 60612 TEL: 312-738-3800 WWW.METRAFIRE.COM
METRAFLEX FIRELOOP™ THREAD ENDS, +/- 4" MOVEMENT		
DRAWN BY: DKISH		DATE: 1/4/2014
APPROVED: ZB		DATE: 1/4/2014
SCALE: NONE	DRAWING NUMBER: MLUT8-REV2	