
MODEL SDFL90 SUCTION DIFFUSER FLEX WITH 150# PLATE FLANGES AND A LR ELBOW



QTY	PART NUMBER	PIPE S INCH	SIZE MM	A	В	PRESSURE RATING (PSI)*	WEIGHT (LBS)	PROJECT INFORMATION
		IINCII	171171			10 111 10 (1 01)	(250)	
	SDFL900200	2"	50	11-1/2"	3-1/4"	516	13	
	SDFL900250	2-1/2"	65	12-1/4"	4''	387	19	
	SDFL900300	3"	80	13"	4-3/4"	316	22	
	SDFL900400	4''	100	14-1/2"	6-1/4"	232	31	
	SDFL900500	5"	125	18"	7-3/4"	191	43	
	SDFL900600	6"	150	19-1/2"	9-1/4"	165	56	
	SDFL900800	8''	200	23-1/4"	12-1/4"	234	104	
	SDFL901000	10''	250	27-1/4"	15-1/4"	230	163	
	SDFL901200	12"	300	31-1/4"	18-1/4"	161	233	
	SDFL901400	14"	350	34-1/4"	21-1/4"	150	275	

*FOR SAFE WORKING PRESSURE ABOVE 70°F, MULTIPLY THE PRESSURE SHOWN AT 70°F TIMES THE CORRECTION FACTOR OF THE REQUIRED TEMPERATURE.

TEMPERATURE (°F)	FACTOR
70	1.0
200	.91
300	.85
400	.78
500	.77
600	.76

CUSTOMER:______
PROJECT:______
ENGINEER:_____

MAX INTERMITTENT OFFSET FROM CENTERLINE 1/8" MAX PERMANENT OFFSET FROM CENTERLINE 3/8"

NSF 372 - LEAD FREE

The wetted surface of this product contacted by consumable water contains less than one quarter of one percent (0.25%) of lead by weight. Material complies with state codes and standards, where applicable, requiring reduced lead content.

REV.	1	TEMP FA	CTOR UPDATE	D DATE	1/4/2017	
for pipe	es in	ro motion	Tex.	2323 W. HUI CHICAGO, TEL: 312-738 FAX: 312-73 WWW.METR	IL 60612 3-3800	
AAODEL CDELCO						

MODEL SDFL90

SDF WITH 150# PLATE FLANGES AND A LR ELBOW

DRAWN BY: D I	KISH	DATE:	11/22/2013	
APPROVED: JC		DATE:	11/22/2013	
	DRAWING NUMBER:			
N/A		SDFL90-1		