


**MODEL VFFG  
VANEFLEX WITH 150# PLATE FLANGE x GROOVED END**



QTY	PART NUMBER	PIPE SIZE		A	PRESSURE RATING (PSI)*	WEIGHT (LBS)	PROJECT INFORMATION
		INCH	MM				
	VFFG0200	2"	50	11-3/4"	516	10	
	VFFG0250	2-1/2"	65	11-3/4"	387	15	
	VFFG0300	3"	80	11-3/4"	316	16	
	VFFG0400	4"	100	11-3/4"	232	21	
	VFFG0500	5"	125	13-1/2"	191	28	
	VFFG0600	6"	150	13-1/2"	165	32	
	VFFG0800	8"	200	15-1/4"	234	56	
	VFFG1000	10"	250	16-1/4"	230	80	
	VFFG1200	12"	300	17-1/4"	161	110	
	VFFG1400	14"	350	17-1/4"	150	120	

\*FOR SAFE WORKING PRESSURE ABOVE 70°F, MULTIPLY THE PRESSURE SHOWN AT 70°F TIMES THE CORRECTION FACTOR OF THE REQUIRED TEMPERATURE.

TEMPERATURE (°F)	FACTOR
70	1.0
200	.91
300	.85
400	.78
500	.77
600	.76

MAX INTERMITTENT OFFSET FROM CENTERLINE 1/8"  
MAX PERMANENT OFFSET FROM CENTERLINE 3/8"


**NSF 372 - LEAD FREE**

The wetted surface of this product contacted by consumable water contains less than one quarter of one percent (0.25%) of lead by weight. Material complies with state codes and standards, where applicable, requiring reduced lead content.

CUSTOMER: \_\_\_\_\_

PROJECT: \_\_\_\_\_

ENGINEER: \_\_\_\_\_

REV. 1	TEMP FACTOR UPDATED	DATE 1/4/2017
		
2323 W. HUBBARD ST. CHICAGO, IL 60612 TEL: 312-738-3800 FAX: 312-738-0415 WWW.METRAFLEX.COM		
<b>MODEL VFFG</b> VF WITH 150# PLATE FLANGE x GROOVED END		
DRAWN BY: <b>DKISH</b>		DATE: <b>11/22/2013</b>
APPROVED: <b>JC</b>		DATE: <b>11/22/2013</b>
SCALE: N/A	DRAWING NUMBER: VFFG-1	