



STANDARD SCREENS

Service	Sizes (in)	Perf. (in)
Steam	2 - 6	.045
	8 - 18	.062
Liquid	2 - 3	.045
	4 - 18	.125

Qty	Part Number	Size I.D. (in)	A (in)	B (in)	C (in)	D (in)	E (in)	Port Size		Blowoff Size (in)	Weight (in)
								1 & 2 (in)	3 (in)		
	TFC0200	2	9-7/8	6-3/16	2-1/2	5	2-1/2	1/2	1	1/2	24
	TFC0250	2-1/2	11-1/4	7-5/8	3	5	3	1/2	1	1	35
	TFC0300	3	12-1/2	8-1/4	3	6	3	1/2	1	1	50
	TFC0400	4	14-7/8	10-1/16	3	7	3	1/2	1	1-1/4	75
	TFC0500	5	17-15/16	12-1/2	3-1/2	9	3-1/2	1/2	1	1-1/4	125
	TFC0600	6	20-3/8	14-5/16	4	10	4	1/2	1	1-1/2	154
	TFC0800	8	24	17-3/8	4	12	4	1/2	1	1-1/2	273
	TFC1000	10	29-1/2	20-7/8	5	15	5	1/2	1	2	464
	TFC1200	12	33-3/4	23-9/16	5	17	5	1/2	1	2	562
	TFC1400	14*	37-1/4	27-13/16	6	19	6	1/2	1	2	906
	TFC1600	16*	42-3/8	29-1/2	6	21	6	1/2	1	2-1/2	1336
	TFC1800	18*	46-1/8	34-1/2	10	24	10	1/2	1	3	1980

LEAD FREE

The wetted surface of this product contacted by consumable water contains less than one quarter of one percent (0.25%) of lead by weight. Material complies with state codes and standards, where applicable, requiring reduced lead content.

OPERATING TEMPERATURE AND PRESSURE:

Steam..... 125 psi at 350°F
 Water, Oil, Gas..... 175 psi at 150°F
 *14" - 18"
 Steam..... 100 psi at 350°F
 Water, Oil, Gas..... 150 psi at 150°F

PROJECT INFO

CUSTOMER: _____

PROJECT: _____

ENGINEER: _____

REV. 1	18" Added	DATE 1/20/2014
		2323 W. HUBBARD ST. CHICAGO, IL 60612 TEL: 312-738-3800 FAX: 312-738-0415 WWW.METRAFLEX.COM
MODEL TF Y-TYPE 125# FLANGED STRAINER		
DRAWN BY: DKISH		DATE: 12/27/2013
APPROVED: JC		DATE: 12/27/2013
SCALE: NONE	DRAWING NUMBER: TF	