


THE I.D. OF COPPER TUBE ENDS
MEETS ASA STANDARD B16.18-1950
AND ASA B16.22-1951



QTY.	MODEL NO.	TO FIT COPPER TUBE		NOM. HOSE I.D.	DIMENSIONS			MAX. WORKING PRESS. AT 70°F **	APPROX. WEIGHT IN LBS.
		NOM. SIZE	ACTUAL O.D.*		A ± 1/4"	B ± 1/8"	C MAX.		
	RAF-2	1/8	1/4	1/4	7-1/2	1/2	.672	450	.19
	RAF-3	1/4	3/8	5/16	8-1/4	5/8	.766	450	.25
	RAF-4	3/8	1/2	3/8	9	3/4	.859	450	.31
	RAF-5	1/2	5/8	1/2	9-3/4	7/8	1.031	450	.44
	RAF-6	5/8	3/4	1/2	10	1	1.031	450	.50
	RAF-7	5/8	3/4	3/4	11-1/4	1-1/8	1.406	340	1.00
	RAF-8	3/4	7/8	3/4	11-1/2	1-1/4	1.406	340	1.06
	RAF-9	1	1-1/8	1	13	1-1/2	1.781	302	1.50
	RAF-10	1-1/4	1-3/8	1-1/4	14-3/4	1-5/8	2.109	280	2.12
	RAF-11	1-1/2	1-5/8	1-1/2	17	2	2.438	245	3.41
	RAF-12	2	2-1/8	2	20	2-1/2	3.078	190	5.53
	RAF-13	2-1/2	2-5/8	2-1/2	24	2-29/32	3.969	320	9.75
	RAF-14	3	3-1/8	3	27	3-13/32	4.422	302	14.62
	RAF-15	3-1/2	3-5/8	3-1/2	32	3-39/32	5.000	150	22.25
	RAF-16	4	4-1/8	4	33	4-13/32	5.406	150	24.78


ALL DIMENSIONS IN INCHES

TESTED AND RECOGNIZED BY UNDERWRITERS LABORATORIES INC.

ALL UNITS CLEANED AND DEGREASED - PACKED IN POLY BAGS.

* Also identified as nominal size refrigeration and automotive tubing.

**Sizes from 2-1/2" employ stainless steel braided hose to assure high pressures.

CUSTOMER _____ PROJECT _____ ENGINEER _____ ARCHITECT _____ PRO. OR P.O. NO _____	
DESCRIPTION: REFRIGERATION VIBRATION ABSORBER	
DRAWN BY: J R	DATE: 12-8-87
DRAWING NO: RAF-1A	